


ITEM.	TYPE.
1	100 K Ω
2	22 K Ω
3	1 M Ω
4	330 Ω
5	22 K Ω
6	10 K Ω
7	1 M Ω
8	220 K Ω
9	100 Ω
10	100 K Ω
11	100 K Ω
12	1 M Ω
13	22 K Ω
14	330 Ω
15	22 K Ω
16	100 K Ω
17	1 M Ω
18	470 K Ω
19	1 M Ω
20	1.5 K Ω
21	220 K Ω
22	100 K Ω
23	220 K Ω
24	1 K Ω
25	0.1 μ F
26	1000 pF
27	0.1 μ F
28	0.01 μ F 1000V.
29	0.1 μ F
30	0.1 μ F
31	8+16 μ F
32	1 μ F
33	0.1 μ F
34	0.01 μ F
35	1000 pF
36	3-8 pF.
37	8-30 pF.
38	1 M Ω
39	100 K Ω
40	1 M Ω
41	5 M Ω +10 M Ω IN PAR
42	1 M Ω
43	100 K Ω
44	500 K Ω
45	100 K Ω
46	EF36
47	GK25
48	EF36
49	GX5GT
50	DG75 OR.
51	1205/8/7.



NB: R8 ADJUST IN TEST AS NECESSARY.

DRN	CHKD:	ISSUE 2: VALVE TYPE	ISSUE 3: 4.11.53.
DATE	APPD:	R8, R19, R22, CHANGED	R18, C4 CHANGED
27.2.53.		ISSUE 1: REDRAWN	ISSUE 4: 24.11.54.
CIRCUIT.			1200B.
INDUSTRIAL ELECTRONICS, DERBY RD, EAST SHEEN, LONDON, S.W.14.			